


SPECIFICATION FOR APPROVAL

COMMODITY	SMD POWER COIL	SPEC NO.	SP-0230418020
ITEM	JNR 252008R-2R2M Green	版本：A	表單編號：QR-012-02

(1) DIMENSION: (UNIT: mm)		DIM.	TOL.
	A	2.50	-0.1/+0.2
	B	2.00	-0.1/+0.2
	C	0.80	Max
	D	0.75	Ref
	E	1.00	Ref

(2) ELECTRICAL CHARACTERISTIC		TEST INSTRUMENTS.
INDUCTANCE	2.2 ± 20% μ H	☐ AGILENT 4294A Precision Impedance Analyzer ☐ Agilent 4287A RF LCR Meter ☐ AGILENT 4285A Precision L.C.R. ☐ HP-4286A RF L.C.R. Meter.
TEST FREQUENCY	1 MHz	☒ CHROMA 3302 Automatic Components Analyzer.
TEST VOLT	1 V	☐ WAYNE KERR 6420 Precision Impedance Analyzer.
RDC	0.150 (typ.) Ω 0.180 (max)	☒ ZENTECH 1320 BIAS CURRENT.
Isat	2.00 (typ.) A 1.80 (max)	☒ BK PRECISION 2840 DC Resistance Meter
Irms	1.80 (1) (typ.) A 2.20 (2)	☒ ZENTECH 502AC Resistance Merter ☐ ADEX AX-1155B DC Low Ohm Meter
Irms	1.60 (1) (max) A 1.80 (2)	☐ WAYNE KERR HI-POT TESTER 7600

REMARK :

Isat : Saturation Current (Isat) will cause L0 to drop approximately 30%.

Irms : Heat Rated Current (Irms) will cause the coil temperature rise approximately ΔT of 40°C

Rated DC current: The lower value of Irms and Isat.


PURCHASER CONFIRMED :

APPROVED	CHECKED	DRAWN
		

TEST REPORT

SPEC NO : SP-0230418020

Typical Performance Curves



Test Instrument :

ZENTECH 3302 Automatic Components Analyzer

ZENTECH 1320 BIAS CURRENT

Testing Condition :

Temperature : 25 to 28°C

Humidity : 60 to 70 % RH

Check by :

姜秀琴

Test by :

陳秀月